



Isomap

Isomap IIB Handheld Device

STRIPPING

of enamelled wire with Swiss precision




Isomap AG
www.isomap.ch
info@isomap.ch



ISOMAP IIB

The Isomap IIB Handheld Device features a sturdy design and allows quick, clean and precise stripping of all standard enamelled wires with a diameter of 0.2 mm to approx. 7.0 mm, and stranded wires up to 4.5 mm in diameter.



HOW TO USE



Insert the enamelled wire into the protective cap and start rotation

Remove the enamelled wire from the protective cap



SPECIAL FEATURES

- High-quality product
- Speed settings on the device
- Easy controls
- Centring of the wire through the screw-on wire guide
- Suitable for a large range of wire diameters
- Strips up to 55 mm off the wire
- Footswitch mode
- Extensive range of accessories

DELIVERY CONTENTS



1. Isomap IIB Handheld Device
2. Stripper head
3. Protective cap
4. Allen Key
5. Regulating pin

Insertable stripper heads

For enamelled wire:

- KG0** Ø 0.2 - 1.2 mm
KG1 Ø 0.75 - 1.5 mm
KG2 Ø 1.5 - 3.0 mm
KG3 Ø 2.2 - 4.5 mm
KG4 Ø 4.0 - 7.0 mm

For stranded wire

- CR1** up to Ø 2.5 mm
CR2 Ø 2 - 4.5 mm

For coaxial wire

- GF** up to Ø 6 mm


ACCESSORIES



Device holder
Part no. 2301



Protective cap with wire guide,
part no. 2486/2491



Footswitch
Part no. 2305



Suction adapter, part no.
2482 (screws onto the
cover cap).



Various stripper heads with
interchangeable blades




Stop pin
Part no. 2392/2393

SPECIFICATIONS

Scope of application	Enamelled wire, stranded wire, coaxial wire
Standard range for enamelled wire	Diameter 0.2 mm to 7 mm
Speed	Infinite settings
Mains voltage	230 V / 50 Hz; 120 V / 60 Hz
Weight	1.31 - 1.47 kg (depending on configuration)

Isomap

www.isomap.ch



STRIPPING

of enamelled wire – with Swiss precision



ISOMAP AG

Obere Bahnhofstrasse 4
CH-3700 Spiez, Switzerland
info@isomap.ch